

TechTopics No. 09

We are often asked to provide estimated heat generation data for our equipment. This issue of TechTopics provides information that allows calculation of approximate heat generated by the type GM38 switchgear under assumed loading conditions.

The heat generation data given in the table is based on full-rated continuous current. Actual heat generation calculations must take into account the true loading of the equipment.

The amount of heat generated is related to the square of the current, so a circuit breaker operating at one-half rated current will have heat generation only one-quarter of that at full-rated continuous current. Because the effect of the square relationship is very significant, it is overly conservative to estimate heat generation based on the assumption that all sections and all circuit breakers each carry their rated continuous current at all times. Air conditioning systems sized based upon such estimates will be much larger than the real operating conditions will require.

Table 1: Approximate full load heat generation (in watts (W)) for type GM38 switchgear (up to 38 kV)

Category	Rated current	Continuous current - circuit breaker (rows 1-3) or main bus (row 4)		
	Actual current	1,200 A	2,000 A	3,000 A
Circuit breaker cell with circuit breaker		461 W	738 W	1,443 W
Vertical section with main bus		211 W	275 W	452 W
Space heaters per vertical section		1,000 W	1,000 W	1,000 W
Voltage transformer (VT) stationary		250 W	250 W	250 W
Control power transformer (CPT) (stationary)		4% of CPT kVA rating	4% of CPT kVA rating	4% of CPT kVA rating
Relaying and instrumentation per circuit breaker cell	Microprocessor type	50 W	50 W	50 W
	Electromechanical non-complex	100 W	100 W	100 W
	Electromechanical complex	200 W to 300 W	200 W to 300 W	200 W to 300 W

Heat generation estimation for type GM38 switchgear (up to 38 kV)

Notes on assumptions:

1. Space heaters, when provided, are not normally controlled by a thermostat. Hence, their load is represented as a continuous load. The purpose of space heaters is to prevent condensation, and this is not limited by the absolute temperature. Even when a thermostat is used to control the heaters, it is set to shut the heaters off at a temperature of approximately 110° F. Therefore, in an air-conditioned room, the heaters would be energized continuously.
2. Heat generated by current transformers is ignored as it is usually insignificant and varies according to the CT ratio as well as the loading.
3. The CPT heat generation estimate is very conservative and assumes the CPT is operated at full-rated capacity. If normal loading is at less than full rating, heat generation may be adjusted by the square of the percent loading.
4. Relaying and instrumentation heat generation estimates are very approximate and are normally estimated on the basis of the number of circuit breaker cells. Extensive relaying and instrumentation may warrant additional conservatism in the estimation of associated heat generation.
5. Conversion factor: watts x 3.415179 = BTU/hour.

Table 2: Calculations

Category	Heat generation	
A	2,000 A circuit breaker at 1,650 A = $738 \times (1,650/2,000)^2 = 502 \text{ W}$	
	1,200 A circuit breaker at 850 A = $461 \times (850/1,200)^2 = 231 \text{ W}$	
	1,200 A circuit breaker at 200 A = $461 \times (200/1,200)^2 = 13 \text{ W}$	
	1,200 A circuit breaker at 600 A = $461 \times (600/1,200)^2 = 115 \text{ W}$	
Total heat generation for circuit breaker cells		861 W
B	Vertical sections with 2,000 A bus at 1,650 A = $5 \times 275 \times (1,650/2,000)^2 =$	936 W
C	Space heaters for five vertical sections = $5 \times 1,000 =$	5,000 W
D	Set of VTs = $1 \times 250 =$	250 W
E	CPT = $1 \times 5\% \times 15 \text{ kVA} =$	600 W
F	Relaying and instrumentation = $4 \times 50 =$	200 W
Total estimated heat generation under assumed loading conditions		7,847 W

To estimate the heat generated under actual loading conditions, determine the component heat generation for each of the components indicated in Table 1. Estimated heat generation for circuit breakers should be adjusted for actual loading based on the ratio of the squares of the actual current and the rated current.

To be precise, this adjustment should also be made for the actual current loading of the main bus for each individual vertical section, but this is frequently ignored in the interest of simplification. Instead, the main circuit breaker loading is usually assumed to be equal to the main bus loading in all vertical sections.

Example: Assume a lineup with five vertical sections, one 2,000 A main circuit breaker (loaded to 1,650 A), three 1,200 A feeder circuit breakers (loading 850 A, 200 A and 600 A), 2,000 A main bus and space heaters. The lineup includes one set of VTs, one 15 kVA CPT and microprocessor relaying, and instrumentation. The calculations would be as described in Table 2.

If true loading were not considered (for example, all calculations performed on the basis of full-rated current), the calculations would yield a heat generation of 9,546 W.

For more information, please contact your local Siemens representative.

Published by and copyright © 2009:
Siemens AG
Energy Sector
Freyeslebenstrasse 1
91058 Erlangen, Germany

Siemens Energy, Inc.
7000 Siemens Road
Wendell, North Carolina 27591 USA

For more information, contact
+1 (800) 347-6659
www.usa.siemens.com/energy

Siemens Energy, Inc.
Order No. E50001-E710-A162-X-4A00

All rights reserved.
Trademarks mentioned in this document are the property of Siemens AG, its affiliates or their respective owners.

Subject to change without prior notice.
The information in this document contains general descriptions of the technical options available, which may not apply in all cases. The required technical options should therefore be specified in the contract.